

# Uniscan OnTrack – A minimalist and multi-talented

## The specialist for galleries as a supplement to existing lighting installations

Compact, flexible and easy to handle: Uniscan brings maximum quality of light to sophisticated art galleries and museums. The neutral, cylindrical shape blends into spaces of all styles, and connection via transadapter makes Uniscan compatible with many existing, dimmable lighting systems. Adaptability is a key feature of Uniscan, because every exhibition needs different light. Light distributions can be changed at any time thanks to the interchangeable

lens units. The darklight lenses give the Uniscan spotlights a magical appearance. Conversion filters as accessories adapt the spectrum. Equally versatile: dimming options and control interfaces, including wireless connectivity via Casambi Bluetooth.



### Uniscan OnTrack for track 220-240V



Structure and characteristics
The features described here are typical of products in this range. Special versions may offer additional or varying features. A comprehensive description of the features of individual products can be found on our website.

### 1 ERCO lenses

- Made of optical polymer
  Darklight lenses: narrow spot, spot,
  flood, wide flood or extra wide flood
- Spherolit lenses: oval flood, oval wide flood or wallwash Zoom lenses: zoom spot or zoom
- oval; continuously focusable
- Projection lenses: narrow framing or wide framing; continuously focus-

### 2 Lens unit

- Rotatable through 360° Polymer, white or black
- Contour spotlights with framing attachment

### 3 ERCO LED-module

- LINCO LED-module
  High-power LEDs: warm white
  (2700K or 3000K) or neutral white
  (3500K or 4000K)
  Collimating lens made of optical
  polymer

- 4 Housing and bracketWhite (RAL9002), black or silverDie cast zinc or cast aluminium,
- powder-coated Pivotable 0°–90° Bracket: cast aluminium/polymer; rotatable through 360° on adapter

- 5 Control gearPhase dimmable+On-board Dim,
- DALI dimmable or Casambi Bluetooth
  Phase dimmable + On-board Dim
  version: Dimming with external
  dimmers (trailing edge) possible and
  rotary control for brightness control on the luminaire

### 6 ERCO transadapter or ERCO DALI transadapter

Variants on request
- Housing: 10,000 further colours
Please contact your ERCO consultant.



Design and application: www.erco.com/uniscan-ontrack

### Uniscan OnTrack for track 220-240V



Darklight lens
The Darklight lens not only creates
a magical impression with just one
light point. It also features precise,
uniform light distributions, wide flexibility in the selection of beam characteristics and state of the art efficiency.



Contour spotlights
Framing attachments enable a sharply defined light beam. In this way fascinating effects can be created with contour spotlights, where crisply illuminated pictures appear to illuminate from within.




Zoom spotlights
The light beam diameter can be infinitely adjusted from spot (15°) to wide flood (65°) by simply turning the lens. Zoom spotlights are particularly suitable for illuminating areas with changing exhibits and merchandise.

| Special characteristics        | Efficient darklight technology | Excellent thermal management         | Phase dimmable +<br>On-board Dim |
|--------------------------------|--------------------------------|--------------------------------------|----------------------------------|
| Efficient darklight technology | Optical cut-off 40°/50°/60°    | EMC-optimised                        | DALI dimmable                    |
| Contour spotlight              | Different light distributions  | Various housing colours              | Casambi Bluetooth                |
| Zoom spotlight                 | Oval flood, freely rotatable   | Various construction sizes           |                                  |
|                                | Different light colours        | Pivotable through 90°                |                                  |
|                                |                                | Accessory for maximum visual comfort |                                  |

### Uniscan OnTrack for track 220-240V - Luminaire arrangement

**Spotlights** Narrow spot, Spot, Flood




### Accentuation

Works of art, merchandise and architectural details are effectively accentuated with Uniscan. The ideal angle of tilt  $(\alpha)$  for this is around 30°. The object is modelled without distorting the effect as a variety of expecting abodywing. It result of excessive shadowing. It also prevents shadows cast by the observer.

Arrangement:  $\alpha = 30^{\circ}$ 

Zoom spotlights Zoom spot, Zoom oval




### Accentuation

Zoom spotlights feature a continuously adjustable beam angle. With the spot to wide flood zoom range, smaller works of art can be accentuated effectively at an inclination angle  $(\alpha)$  of approximately 30°. The oval zoom is suitable for linear works of art. The object is modelled without distorting the effect as a result of excessive shadowing. It also prevents shadows cast by the observer.


Arrangement:  $\alpha = 30^{\circ}$ 

Contour spotlights Narrow framing, Wide framing




### Projection

Contour spotlights generate freely adjustable, crisp-edged light beams. As a result fascinating effects can he created where pictures appear to illuminate from within. Select narrow framing to accurately illuminate small exhibits from a long distance and wide framing to accurately illuminate large exhibits from a short distance.



### **Floodlights** Wide flood, Extra wide flood, Oval

wide flood, Oval flood




Washlighting The ideal angle of tilt ( $\alpha$ ) for floodlighting objects with a long, square shape, e.g. pictures, sculptures or merchandise displays, is around

Arrangement:  $\alpha = 30^{\circ}$ 


### Uniscan OnTrack for track 220-240V – Luminaire arrangement

**Lens wallwashers** Wallwash



Wallwashing
For uniform vertical lighting, the distance to the wall (a) of Uniscan lens wallwashers should be around one third of the room height (h). This results in an angle of tilt  $(\alpha)$  of approx. 35°.

Arrangement:  $a = 1/3 \times h$  or  $\alpha = 35^{\circ}$ 





For good longitudinal uniformity, the spacing (d) of Uniscan lens wallwashers may be up to 1.2 times the distance to the wall (a).

Arrangement:  $d \le 1.2 \times a$ 

Optimal wall distances and luminaire spacing values for individual products are specified in the wallwasher tables at www.erco.com.

### Uniscan OnTrack for track 220-240V





<sup>\*</sup> available on request

Article numbers and planning data: www.erco.com/022635

Design and application: www.erco.com/uniscan-ontrack



